

**Manufacturer's Declaration of Conformity**  
(in accordance with ISO/IEC 17050-1)

**Issuer's name:** Tuttnauer Europe B.V.  
**Issuer's address:** Hoeksteen 11  
P.O. Box 7191  
4800 GD Breda  
The Netherlands

**Object of the declaration:** Laboratory Autoclaves  
**Model Codes:** See Addendum: product list

**In addition we ensure and declare that the distributed products, as mentioned, meet the relevant provisions.**

Document	Title
- Directive 2006/42/EC	Machine Directive
- Directive 2014/35/EU	Low Voltage Directive
- Directive 2014/30/EU	EMC Directive
- Directive 2014/68/EU	Pressure Equipment Directive
- EN 61326-1:2013	Electrical equipment for measurement, control and laboratory use EMC requirements
- EN 61010-1:2010	Safety requirements for electrical equipment for measurement, control and laboratory use
- EN 61010-2-040:2015	Safety requirements for sterilizers and washer-disinfectors used to treat medical materials.

All harmonized standards which are applicable to the object, as published in the Official Journal of the European Communities.

**Additional information:**

**Notified Body:** Dekra Certification BV  
Meander 1051  
6825 MJ Arnhem  
The Netherlands

**First issue date certificate:** February 14, 2010  
**Valid until:** February 1, 2024

This documentation is supported by the Quality Management System certification based on the harmonized standard ISO 9001:2015, Quality Management System Certificate with reference numbers: 2129743, issued for the 1<sup>st</sup> time on February 14, 2010, and delivered by Dekra Certification

**Signed for and on behalf of:** Breda, The Netherlands, 18 April 2021

**Name:** Keren Ziv

**Function:** QA&RA Manager, Tuttnauer Europe B.V

**Signature:** 

**ADDENDUM: Product List**

**Laboratory Series**

Model	Inner Dimensions Diameter x Depth (mm)	Volume  Liters
<b>EL-D Series - Fully Automatic</b>		
2840EL-D	280 x 400	28
3850EL-D	380 x 500	65
3870EL-D	380 x 690	85
5075EL-D	500 x 750	160
<b>ELC-D Series - Fully Automatic with Rapid Cooling</b>		
3850ELC-D	380 x 500	65
3870ELC-D	380 x 690	85
5050ELC-D	500 x 500	110
5075ELC-D	500 x 750	160
<b>ELV-D Series - Fully Automatic, Vertical</b>		
2840ELV-D	280 x 460	31
3850ELV-D	380 x 500	65
3870ELV-D	380 x 690	85
5050ELV-D	500 x 500	110
5075ELV-D	500 x 750	160
<b>ELVC-D Series - Fully Automatic, Vertical, with Rapid Cooling</b>		
3850ELVC-D	380 x 500	65
3870ELVC-D	380 x 690	85
5050ELVC-D	500 x 500	110
5075ELVC-D	500 x 750	160

The affix letters: + BH, C, F, G, PV, W, WR, WS may be added to the device label including combination of these letters.