

FURTHER INFORMATION AT
WWW.VACUUBRAND.COM



ONE-STAGE DIAPHRAGM VACUUM PUMPS
SUITABLE FOR SINGLE AND PARALLEL LAB
APPLICATIONS

DIAPHRAGM VACUUM PUMPS

ME 2 NT AND ME 2C NT

vacuubrand

Technology for Vacuum Systems

One-stage diaphragm pumps are an excellent solution for continuous, oil-free pumping of gases and vapors at low vacuum requirement. In contrast to waterjet pumps they do not consume water and therefore do not produce any contaminated waste water in daily use. Typical applications are vacuum ovens, filtrations and multi-port manifolds for medium throughput, as well as pumping of gases and oil-free evacuation in general. The one-stage construction provides the advantageous combination of high pumping speed and low ultimate vacuum down to 70 mbar.

■ Diaphragm pump ME 2 NT

Diaphragm vacuum pumps are an excellent choice for applications with non-corrosive gases and vapors. The materials used in these pumps like aluminum and special plastics are opening a wide range of applications. The highly flexible fabric-reinforced double diaphragm made of FKM is ideal for extended operating life.

■ Chemistry diaphragm pump ME 2C NT

One-stage chemistry diaphragm vacuum pumps are an excellent choice for applications with corrosive gases and vapors which do not require very deep vacuum levels. Typical applications are vacuum ovens, filtrations as well as concentration of solvents with low boiling points. All major parts in contact with pumped media are made of chemically resistant fluoroplastics. The well proven robust PTFE sandwich diaphragm provides outstanding reliability and operating life.



Vacuum regulation valve (mbar/torr) for non-corrosive gases

PERFORMANCE FEATURES

- whisper quiet and very low vibration
- powerful, even for parallel operation of several applications
- high performance even at low vacuum levels
- high chemical resistance especially with ME 2C NT
- long diaphragm life, maintenance-free drive system



VACUU · LAN® Mini-Network: 3 adjustable ports with built-in check valves against interference at parallel applications (e.g., filtrations)

TECHNICAL DATA		ME 2 NT	ME 2C NT
Number of heads / stages		1 / 1	1 / 1
Max. pumping speed at 50/60 Hz	m ³ /h	2.0/2.2	2.1/2.4
Ultimate vacuum (abs.)	mbar	70	70
Max. back pressure (EX) (abs.)	bar	2	1.1
Inlet connection (IN)		Hose nozzle DN 10 mm	Hose nozzle DN 10 mm
Outlet connection (EX)		Silencer / G1/4"	Hose nozzle DN 10 mm
Rated motor power	kW	0.18	0.18
Dimensions (L x W x H), approx.	mm	243 x 211 x 198	243 x 211 x 198
Weight, approx.	kg	10.2	10.2

ORDERING INFORMATION		ME 2 NT	ME 2C NT
230 V ~ 50-60 Hz	CEE	730000	730100
230 V ~ 50-60 Hz	UK	730002	730102
100-115 V ~ 50-60 Hz, 120 V ~ 60 Hz	US	730003	730103
With NRTL certification for Canada and the USA			

ACCESSORIES	ME 2 NT
Rubber vacuum tubing DN 10 mm (686002)	
VACUU · LAN® Mini-Network (2614455)	
Vacuum regulation valve with manometer (696840)	

ACCESSORIES	ME 2C NT
Rubber vacuum tubing DN 10 mm (686002)	
VACUU · LAN® Mini-Network (2614455)	